



QUICKCONNECT T600RO

3-STAGE TANKLESS REVERSE OSMOSIS SYSTEM



APPLICATIONS

- ◆ Drinking water

FEATURES • BENEFITS

- ◆ Quick connect filter replacement with twist and lock feature
- ◆ LED light indicator on smart faucet alerts you when it's time to change the filter
- ◆ Enjoy better water with up to 96.8% reduction of Total Dissolved Solids (TDS)
- ◆ Convenient vertical under sink unit with no need for a storage tank

INSTALLATION TIPS

- ◆ System will stand vertically with the front cover facing outward for ease of changing cartridges.
- ◆ Prior to installation, turn off cold water line and allow all water to drain from line.
- ◆ Ensure an electrical outlet is available and nearby for the system. System is equipped with an appliance-grounding conductor and grounding plug.


OPERATION TIPS

- ◆ Replace pre/post filters every 12 months and RO membrane every 24 months.
- ◆ Place replacement cartridges in correct slots by matching RO, CF, CB left of the slot.
- ◆ System is designed with light indicators to notify when ready to change out cartridges.

INCLUDES

- ◆ System with 2 filters & 1 membrane
- ◆ Installation hardware kit
- ◆ Smart LED drinking water faucet

QUICKCONNECT T600RO 3-STAGE TANKLESS REVERSE OSMOSIS SYSTEM



SPECIFICATIONS

- ◆ **Systems (Model/Part No.)**
T600RO/4006877
- ◆ **System Dimensions**
5.51"W x 17.60"D x 17.10"H
(140 mm x 447 mm x 434 mm)
- ◆ **System Weight**
25.35 lbs (11.5 kg)
- ◆ **Contaminant Reduction**
TDS
- ◆ **TDS Rejection**
96.8%
- ◆ **Approximate Filter Life***
Pre/Post Filters: 12 months
RO Membrane: 24 months
- ◆ **System Production Rate**
396.40 gpd (1500 Lpd)
(Side Faucet Required)
- ◆ **Recovery Rating**
57.5%
- ◆ **Certifications**
NSF/ANSI Standard 58
- ◆ **Feed Pressure Range**
10 - 60 psi (0.69-4.14 bar)
- ◆ **Temperature Range**
40 - 100°F (4.4 - 37.8°C)
- ◆ **Replacement Cartridges**
(Model/Part No.)
ROM-24M / 4006882
CF-12M & CB-12M / 4006943

* Filter life dependent on gallon usage and overall incoming water quality.



System tested and certified by NSF against NSF/ANSI standard 58 for the reduction of the claims specified on the performance data sheet when used in system T600RO.



13845 Bishops Dr. | Suite 200 | Brookfield, WI 53005 | United States
P: 262.238.4400 | Customer Service: 800.279.9404 | tech-support@pentair.com | pentair.com

All indicated Pentair trademarks and logos are property of Pentair. Third party registered trademarks and logos are the property of their respective owners.

© 2023 Pentair. All rights reserved.

4006953 JE23